

We Hamilton Bonaduz AG, CH-7402 Bonaduz/Switzerland confirm that the following products

Product families **pH Arc sensors** (including MecoTrode Arc)

ORP Arc sensors

DO Arc sensors (including VisiFerm DO)
Conducell Arc sensors (excluding SU)
Incyte Arc sensors (excluding SU)

Item Number REF

See product list

meets the following EU directives (including all applicable amendments):

CE

EMC Directive

2014/30/EU

RoHS 2 Directive

2011/65/EU + 2015/863/EU

Applied company quality management system

EN ISO 9001: 2015

Certification Body

TÜV Rheinland Industrie Service GmbH

Am Grauen Stein 29

D-51105 Köln-Poll, Germany

Applied standards

EMC Directive

EN 61326-1: 2013

Emission: Class B

Immunity:

Industrial electromagnetic environment

RoHS 2 Directive:

EN IEC 63000: 2018

Additional Information:

Concerning China RoHS ("Restricted Use of Hazardous Substances in Electronic and Electrical Products"), the sensors listed here are marked with . For the Hazardous Substances Table, see www.hamiltoncompany.com

Authorize department for technical documents:

HAMILTON Process Analytics

Hamilton Bonaduz

CEO

Bonaduz, 20.05, Jola



pH Arc Sensors

This Declaration of Conformity applies to all Hamilton pH Arc sensors where the product name is in agreement with the following generic product name definition:

Polilyte Plus *** Arc ***
EasyFerm Plus *** Arc ***
EasyFerm Bio *** Arc ***
MecoTrode *** Arc ***

How to read this generic product name definition?

- a) The 1st group of *** represents the type of pH glass used: for example "PHI", "HF", "H" or others
 If the pH glass is not explicitly mentioned in the product name, then
 - EasyFerm Plus is equipped with PHI glass
 - EasyFerm Bio is equipped with HB glass
 - Polilyte Plus and MecoTrode are equipped with H glass
- b) The second group of *** represents the a-length of the sensor, for example "120" (mm). The a-length must be within 50 to 600 mm.

MecoTrode *** Arc Sensors

REF	Sensor
10110152	MecoTrode H Arc 120
divers	MecoTrode H Arc ***

ORP Arc Sensors

Ref	Sensor
243050	EasyFerm Plus ORP Arc 120
243051	EasyFerm Plus ORP Arc 225
243052	EasyFerm Plus ORP Arc 325
243053	EasyFerm Plus ORP Arc 425
divers	EasyFerm Plus ORP Arc ***
243060	Polilyte Plus ORP Arc 120
243061	Polilyte Plus ORP Arc 225
243062	Polilyte Plus ORP Arc 325
243063	Polilyte Plus ORP Arc 425
divers	Polilyte Plus ORP Arc ***



DO (Dissolved Oxygen) Arc Sensors (including VisiFerms)

This Declaration of Conformity applies to all Hamilton dissolved oxygen DO Arc sensors where the product name is aligned with the following generic product name definition:

VisiFerm DO Arc *** xx

VisiFerm DO ECS *** xx

VisiFerm DO SU Arc ***

VisiWater DO Arc 120 FCyy

VisiWater DO P Arc FCyy

OxyFerm FDA Arc ***

OxyGold G Arc ***

OxyGold B Arc ***

Note 1: *** represents the a-length of the sensor, e.g "120" (mm). The a-length must be within 120 to 600 mm.


Note 2: The xx represents the sensing device

Note 3: the yy represents the length of the fixed cable, yy = 0..25m



Conducell Arc Sensors

This Declaration of Conformity applies to all Hamilton Conducell 4U*F Arc sensors where the product name is aligned with the following generic product name definition:



In addition to the generic product name definition the following products are also certified:

Ref	Sensor
242159	Conducell 4USF Arc PG-120
242160	Conducell 4USF Arc PG-225
242161	Conducell 4USF Arc PG-325
242162	Conducell 4USF Arc PG-425
divers	Conducell 4USF Arc PG-***
10/10/20	
243578	Conducell UPW Arc TC 1.5"
243579	Conducell UPW Arc PG 13.5
divers	Conducell UPW Arc TC 1.5" ***
divers	Conducell UPW Arc PG 13.5 ***



Incyte Arc Sensors

This Declaration of Conformity applies to all Hamilton **Incyte Arc sensors** where the reference number is aligned with the following generic product name definition:

Ref	Sensor
243950-0**1	Incyte Arc 120
243950-0**2	Incyte Arc 220
243950-0**3	Incyte Arc 320
243950-0**4	Incyte Arc 420

License(s)

- 00

- 01

- 10

- 11 - 20

- 21

(mandatory)

none

Recording

Scan

Scan + Recording

Scan + Correlation

Scan + Correlation + Recording